

Mon|Lun | **02 Mar** | 2015

IN COLLABORAZIONE CON MIDO, SUPPLEMENTO DI
OTICA ITALIANA

OKIA

“HD Sparkle”,
the new feminine style

“HD Sparkle”, la nuova
montatura femminile



Okia is proud to present “HD Sparkle”, a really surprising blend of high technology and fashion that will seduce the feminine public through its glamorous elegance. Inspiration can come from anywhere and, thanks to the incredible creative opportunities opened by its patented HDA Technology, Okia is able to translate every single inspirational image or idea into extremely detailed and lifelike eyewear decorations. In order to meet the needs of the most sophisticated and demanding women, Okia has developed “HD Sparkle”, an extraordinary feminine style with real lace decorations. Although inserting a real fabric into acetate is really difficult, Okia has managed to obtain an extremely smooth, regular and tidy effect thanks to the application of the HDA Technology. The lace decoration can be realized in different colours and combined with Csb (Crazy Sparkling Beauty) technique, an advanced application of HDA Technology that combines acetate with shining materials and allows random or controlled patterns with an extraordinary non-delaminated effect.



Okia presenta “HD Sparkle”, una sorprendente miscela di tecnologia all'avanguardia e moda che sedurrà il pubblico femminile con la sua eleganza e il suo glamour.

L'ispirazione può provenire da qualsiasi cosa e, grazie alle incredibili opportunità creative offerte dalla brevettata HDA Technology, Okia è in grado di tradurre ogni singola immagine o idea ispiratrice in decorazioni eyewear estremamente dettagliate e realistiche. Per soddisfare i desideri delle donne più sofisticate ed esigenti, Okia ha sviluppato “HD Sparkle”, uno straordinario modello femminile con decorazioni in vero pizzo.

Benché l'inserimento di vero tessuto nell'acetato sia un'operazione molto difficile, Okia è riuscita a ottenere un effetto incredibilmente liscio e regolare grazie all'applicazione della HDA Technology. La decorazione in pizzo può essere realizzata in diversi colori e può essere abbinata alla tecnica Csb (Crazy Sparkling Beauty), un'applicazione avanzata della HDA Technology che combina l'acetato con materiali luccicanti dando vita a pattern casuali o controllati con uno straordinario risultato non delaminato.

Okia
Pad. 4
Stand
H23, K26



A TOPCON EXAM SOLUTION

New CA-800 Topographer



- » Fluorometry
- » Pupillometry
- » Zernike Analyse
- » Database on-board
- » Meibography
- » Capacitive 10.1 touch screen
- » Complete corneal analysis

Discover the new CA-800, booth G27, H30 (hall 3)

TOPCON EUROPE MEDICAL B.V.
Cappellestraat 23/25 • 3000 Leuven • Belgium
T: +31 (0)40 - 458 50 77 F: +31 (0)40 - 284 49 40
E-mail: medical@topcon.eu, www.topcon-medical.eu

PERFORMANCE
YOU CAN COUNT ON
TOPCON